6/10/2014

Product Details

Product 21445 Number:

Order F15T12/350BL/500/PH Abbreviation:

General 22W T12 preheat fluorescent lamp, Blacklight phosphor **Description:** (356 nm), 500 mA

## \* Full Case Required

Product Information	
Abbrev. With Packaging Info.	F15T12350BL500PH 30/CS 1/SKU
Base	M edium Bip in
Bulb	T12
Nominal Wattage (W)	22.00

## Footnotes

- Approximate initial lumens after 100 hours operation.
- The life ratings of fluorescent lamps are based on 3 hr. burning cycles under specified conditions and with ballast meeting ANSI specifications. If burning cycle is increased, there will be a corresponding increase in the average hours life.
- Starter required.
- These lamps are not intended and should not be used for diagnostic, therapeutic, or cosmetic purposes.
- CAUTION: This lamp emits ultraviolet (UV) power during operation and is in Risk Group 2 per ANSI/IESNA RP-27.3-96. Exposure at less than 0.6 meters (24 inches) should be limited; for example exposure at 0.45m (18 inches) should not exceed 4 hoursin an 8 hour interval (see ANSI/IESNA RP-27.1-96). Certain medications and chemicals can increase an individual's sensitivity. Consult your physician for specific information. Protective eyewear should be worn in occupational situations involving long term exposure in close proximity to the lamp. This lamp is not intended and should not be used for diagnostic, theraputic or cosmetic purposes.